# armfield

SOFTWARE INCLUDED WITH ALL F1-10 BENCH'S AS STANDARD

# F SERIES: BASIC FLUID MECHANICS Complete Fluid Mechanics Laboratory – F1

## **Energy Losses in Pipes - F1-18**



The unit consists of a vertical test pipe on the side of the equipment which can be fed directly from the hydraulics bench supply or, alternatively, from the integral constant head tank above.

These in turn provide high or low flow rates which may be controlled by a valve at the discharge end of the test pipe. Manometers are used to measure the head loss.

For large pressure differentials a digital handheld manometer is used. In addition, a pressurised water manometer for small pressure differentials is also fitted to the unit.

### **Experimental content**

- ➤ To investigate the head loss due to friction in the flow of water through a pipe and to determine the associated friction factor over a range of flow rates in laminar flow
- ➤ To investigate the head loss due to friction in the flow of water through a pipe and to determine the associated friction factor over a range of flow rates in turbulent flow
- ▶ Determining the critical Reynolds number

### Description

The Energy Losses in Pipes accessory consists of a test pipe, orientated vertically on the side of the equipment, which may be fed directly from the hydraulics bench supply or, alternatively, from the integral constant head tank.

These sources provide high or low flow rates which can be controlled by a valve at the discharge end of the test pipe. Head loss between two tapping points in the test pipe is measured using two manometers, digital hand held manometer for large pressure differentials and a pressurised water manometer for small pressure differentials.

Excess water discharging from the constant head tank is returned to the sump tank of the hydraulics bench.

Adjustable feet permit levelling.

# Technical specifications Diameter of test pipe 3.0mm Length of test pipe 760mm Distance between pressure tapping points Range of the digital manometer 103 kPa Range of water manometer 500mm

Requires Hydraulics Bench Service unit F1-10/F1-10-2

Measuring cylinder capacity

Overall dimensions	
Length	0.33m
Width	0.28mm
Height	0.75m

1000ml

UK office - email: sales@armfield.co.uk tel: +44 (0) 1425 478781 (for ROW) USA office - email: info@armfield.inc tel: +1 (609) 208-2800 (USA only)



We reserve the right to amend these specifications without prior notice. E&OE © 2022 Armfield Ltd. All Rights Reserved

URL: http://www.armfield.co.uk/f1